

Software History

Signateq®

Version	Date	History
2.08	09.07.2026	- Custom calibration at zero force position improved - Improved initial offset calculation
2.06	18.06.2026	- New signal clipping detection* - Improved initial offset calculation with preload* *Requires at least XENAX® firmware V8.18A.
2.04	22.12.2025	- Support for torque sensor up to 80Nm including new XENAX® ASCII commands SQST, SQTD, SQSTT, SQSNT and CLTOI* - Extended range of force sensor up to 2kN* - Extended ASCII command CLFOI supporting initial offset request *Requires at least XENAX® firmware V8.16.
2.02	19.09.2025	- Fixes custom calibration compression/tension & tension entry calculation
2.01	14.02.2022	- Improved sensitivity adjustment capabilities for all three load directions - Support for new XENAX® ASCII commands SQAC and SQCM, requires at least XENAX® firmware V5.10B
2.00	10.12.2021	- Support for three calibration types “test report”, “custom calibration” and “factory calibration”
1.04	30.08.2021	- Support for hardware revision 2.0 - General timing optimizations
1.02	26.08.2020	- First Release